







## Technische Hinweise

Trafo: prim 220 V~/50 Hz / 1,50 A  
sek. 5 V~/80 mA

Akku: 3 Zellen 3,6 V  
2 Zellen 2,4 V

Betrieb: 3,6 V ca. 6 Minuten  
2,4 V ca. 4 Minuten

Saugleistung 13 mbar



08 3372  
NL1  
08 8581  
D1

51 1401  
NL1,D1  
Gebrauchsanweisung  
(D,GB,F,I,NL,N,S,SF)

1) 02 5102

2) 02 5570  
NL1  
03 2466  
D1

3) 02 5591  
NL1  
02 5150  
D1